



■ FDA1055 ■


Inductance Range: 0.56~4.7μH

DIMENSIONS／外形寸法図



Recommended patterns

推奨パターン図



FEATURES／特長

- 11.7×10.8mm square and 5.5mm Max. height.
- Magnetically shielded, low DC resistance.
- Suitable for large current
- The use of magnetic metal alloy powder ensure capability for large current.
- Low audible core noise.
- Ideal for DC-DC converter applications in hand held personal computer and etc.
- RoHS compliant.

- 11.6×10.8mm 角、高さ 5.5mm Max.
- 閉磁路、低直流抵抗
- 大電流対応
- 磁性材に合金系磁性粉を用いた大電流対応
- 低コア鳴きノイズ
- ノートパソコンなどのDC-DC コンバータなどに最適
- RoHS指令対応

SELECTION GUIDE FOR STANDARD COILS

TYPE FDA1055 (Quantity/reel; 500 PCS)

東光品番	インダクタンス ⁽¹⁾	許容差	直流抵抗 ⁽²⁾	直流重量許容電流 ⁽³⁾	温度上昇許容電流 ⁽⁴⁾
TOKO Part Number	Inductance ⁽¹⁾ (μH)	Tolerance (%)	DC Resistance ⁽²⁾ (mΩ) Max. (Typ.)	Inductance Decrease Current ⁽³⁾ (A) Max. (Typ.) $\frac{\Delta L}{L} = 20\%$	Temperature Rise Current ⁽⁴⁾ Δ T=40°C (A) Max. (Typ.)
FDA1055-R56M	0.56	±20	1.8 (1.42)	27.7 (36.9)	22.7 (28.4)
FDA1055-1R2M	1.2	±20	2.9 (2.34)	20.0 (26.6)	17.9 (22.4)
FDA1055-1R5M	1.5	±20	3.5 (2.80)	18.0 (24.0)	16.6 (20.8)
FDA1055-2R2M	2.2	±20	4.8 (3.94)	15.5 (20.6)	13.6 (17.0)
FDA1055-3R3M	3.3	±20	7.3 (5.92)	11.7 (15.6)	11.2 (14.0)
FDA1055-4R7M	4.7	±20	11.0 (8.7)	9.9 (13.1)	9.1 (11.4)

(1) Inductance is measured with a LCR meter 4284A (Agilent Technologies) or equivalent.

Test frequency at 100KHz

(2) DC resistance is measured with 34420A (Agilent Technologies) or 3541(HIOKI). (environment temp. of 25°C)

(3) Inductance Decrease Current based upon 20% inductance reduction from the initial value

(4) Temperature Rise Current based upon 40°C temperature rise.
(Reference ambient temperature 20°C)

(5) Absolute maximum voltage 30VDC.

(1) インダクタンスはLCR メータ4284A (Agilent Technologies) または同等品により測定する。

測定周波数は100KHzです。

(2) 直流抵抗は測定器34420A (Agilent Technologies) または3541(HIOKI)と同等品により測定する。(周囲温度25°C)

(3) 直流重量許容電流：直流重量電流を流した時インダクタンスの値が初期値より20%減少する直流電流値

(4) 温度上昇許容電流：コイルの温度が40°C 上昇する値 (周囲温度25°Cを基準とする。)

(5) 絶対最大電圧 30VDC

NOTICE: Please be sure that you carefully discuss your planned purchase with our sales division if you intend to use the product for business use etc. is severe.

御注意：業務用など、厳しい使用条件でのご使用をご検討の場合
は必ず事前に弊社営業窓口までご相談ください。