

# Biased Detector With 50 Ohm SMA Male to SMA Female Video Out Operating From 8 GHz to 18 GHz



### **TECHNICAL DATA SHEET**

PE8008

Biased Detector With 50 Ohm SMA Male to SMA Female Video Out Operating From 8 GHz to 18 GHz

Configuration

Bias Type Biased
Detector Polarity Negative
Body Style Straight
RF Input Connector SMA Male
RF Input Impedance 50 Ohms
Video Output Connector SMA Female

**Electrical Specifications** 

Frequency Range, GHz

Voltage Sensitivity, mV/mW

1,600

Tangential Signal Sensitivity
-52

Flatness, dB

0.7

Maximum Input Power, Watts

Video Capacitance, pF

8 to 18

0,600

1,600

23

10

**Mechanical Specifications** 

**Temperature** 

Operating Range,deg C -55 to +125 Storage Range, deg C -65 to +150

**RF Input** 

Type SMA Male Hex Size, Inch 5/16

**Video Output** 

Type SMA Female

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant Yes

Plotted and Other Data

Notes: Values at 25 °C, sea level

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Biased Detector With 50 Ohm SMA Male to SMA Female Video Out Operating From 8 GHz to 18 GHz PE8008

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

ISO 9001 : 2008 Registered



# Biased Detector With 50 Ohm SMA Male to SMA Female Video Out Operating From 8 GHz to 18 GHz



### **TECHNICAL DATA SHEET**

PE8008

Biased Detector With 50 Ohm SMA Male to SMA Female Video Out Operating From 8 GHz to 18 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Biased Detector With 50 Ohm SMA Male to SMA Female Video Out Operating From 8 GHz to 18 GHz PE8008

URL: http://www.pasternack.com/negative-biased-schottky-diode-detector-80-180-ghz-pe8008-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

ISO 9001 : 2008 Registered

## PE8008 CAD Drawing

Biased Detector With 50 Ohm SMA Male to SMA Female Video Out Operating From 8 GHz to 18 GHz

